

TECHNICAL NEWS

[Issue No.] LVS-YE-0002

[Page] 1/1

[Title] Correnction of product weight

[Date of Issue] January 2020

[Relevant Models] Air Circuit Breakers World Super series <Type : AE-SW/SWA>

We correct errors found in our catalog of Mitsubishi Low Voltage Air Circuit Breakers “Y-0622”, Instruction manual “IB63366”, and Low Voltage Circuit Breakers <General Catalog> “Y-0720” as shown in the table below.

The specifications of breakers are not changed due to this correction.

We are terribly sorry to cause you inconvienience by this.

Table 1 Product weight

Type	Connection	< Correct >		< Incorrect >	
		3 Pole	4 Pole	3 Pole	4 Pole
AE630-SW	Fixed type	35	42	40	50
	Drawout type	56	70	63	77
	Cradle only	24	28	26	30
AE1000-SW	Fixed type	35	42	41	51
	Drawout type	56	70	64	78
	Cradle only	24	28	26	30
AE1250-SW	Fixed type	35	43	41	51
	Drawout type	56	70	64	78
	Cradle only	24	28	26	30
AE1600-SW	Fixed type	35	43	42	52
	Drawout type	56	70	65	79
	Cradle only	24	28	26	30
AE2000-SWA	Fixed type	44	54	47	57
	Drawout type	62	75	70	84
	Cradle only	27	32	31	35
AE2000-SW	Fixed type	51	64	60	72
	Drawout type	81	101	92	113
	Cradle only	33	40	35	43
AE2500-SW	Fixed type	52	64	61	73
	Drawout type	81	101	93	114
	Cradle only	33	40	35	43
AE3200-SW	Fixed type	54	67	63	75
	Drawout type	85	106	95	116
	Cradle only	34	42	36	44
AE4000-SWA	Fixed type	73	92	81	99
	Drawout type	101	127	108	136
	Cradle only	46	58	49	61
AE4000-SW	Fixed type	141	159(HN) 179(FN)	160	180(HN) 200(FN)
	Drawout type	194	223(HN) 247(FN)	233	256(HN) 279(FN)
	Cradle only	98	113(HN) 127(FN)	118	133(HN) 148(FN)
AE5000-SW	Fixed type	141	159(HN) 179(FN)	160	180(HN) 200(FN)
	Drawout type	194	223(HN) 247(FN)	233	256(HN) 279(FN)
	Cradle only	98	113(HN) 127(FN)	118	133(HN) 148(FN)
AE6300-SW	Fixed type	148	166(HN) 188(FN)	160	180(HN) 200(FN)
	Drawout type	208	238(HN) 269(FN)	240	263(HN) 286(FN)
	Cradle only	107	121(HN) 138(FN)	125	140(HN) 155(FN)

Note1. Above weights include an electronic trip relay, but don't include the other accessories..

Note2. Above values are measured values and can be used only for reference.