



TYPE APPROVAL CERTIFICATE

Certificate no.:
TAE00003NE
Revision No:
2

This is to certify:
that the Circuit Breaker

with type designation(s)
AE630-SW - AE4000-SWA

issued to
Mitsubishi Electric Corporation Fukuyama Works
Fukuyama City, HIROSHIMA, Japan

is found to comply with
DNV rules for classification – Ships, offshore units, and high speed and light craft

Application:

Products approved by this certificate are accepted for installation on all vessels classed by DNV.

Rated voltage (V) up to 690
Rated current (A) up to 4000

Issued at **Høvik** on **2024-09-04**

for **DNV**

This Certificate is valid until **2029-09-03**.

DNV local unit: **Kobe**

Approval Engineer: **Qiang William Guo**

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to USD 300 000.



Name and place of manufacturer

Mitsubishi Electric Low Voltage
 Equipment (Xiamen) Co., Ltd
 Fujian Province,
 P.R. China

Product description

Low voltage circuit breakers Type AE-SW(A):

Type	AE630-SW	AE1000-SW	AE1250-SW	AE1600-SW	AE2000-SWA
Rated insulation voltage AC (V)	1000	1000	1000	1000	1000
Rated operational voltage AC (V)	690	690	690	690	690
Rated Current (A)	125-630*	400-1000*	625-1250*	800-1600*	1000-2000*
Rated Frequency Hz	50-60	50-60	50-60	50-60	50-60
Rated Short-circuit Service Breaking cap (Icu/Ics)					
690V	65/65	65/65	65/65	65/65	65/65
Power factor	0.23	0.23	0.23	0.23	0.17/0.23
500V	65/65	65/65	65/65	65/65	65/65
Power factor	0.16	0.16	0.16	0.16	0.16
Utilization category	B	B	B	B	B
Rated Short-current withstand current cap. 1 sec. (Icw)					
690 V	65	65	65	65	65
500 V	65	65	65	65	65

Type	AE2000-SW	AE2500-SW	AE3200-SW	AE4000-SWA
Rated insulation voltage AC (V)	1000	1000	1000	1000
Rated operational voltage AC (V)	690	690	690	690
Rated Current (A)	625-2000*	1250-2500*	1600-3200*	2000-4000*
Rated Frequency Hz	50-60	50-60	50-60	50-60
Rated Short-circuit Service Breaking cap (Icu/Ics)				
690V	75/75	75/75	75/75	75/75
Power factor	0.17/0.23	0.17/0.23	0.17/0.23	0.17/0.23
500V	85/85	85/85	85/85	85/85
Power factor	0.17/0.18	0.17/0.18	0.17/0.18	0.17/0.18
Utilization category	B	B	B	B
Rated Short-current withstand current cap. 1 sec. (Icw)				
690 V	75	75	75	75
500 V	75	75	75	75

* Fixed

Application/Limitation

Location Classes:
 Temperature: B, Humidity: B, Vibration: A, EMC: A, Enclosure: IP20,

Type Approval documentation

Technical info:

"Low voltage breaker specification", part of Mitsubishi documents "Low voltage breaker AE630-SW ~ AE1600-SW AE2000-SWA, Specification and construction" and "Low voltage breaker AE2000-SW ~ AE3200-SW AE4000-SWA, Specification and construction".

Test reports:

Mitsubishi EMC Test report doc. No. ETR-21-171-03 dated 2021-03-25

Mitsubishi test report (EMC) LEN 046085-A, dated 2004-11-05, Mitsubishi environmental test report LEN040107 dated 2004-12-21.

Mitsubishi report "Type test data" for AE630-SW, AE1000-SW, AE1250-SW, AE1600-SW and AE2000-SWA dated 2004-11-04. Mitsubishi report "Type test data" for AE2000-SW, AE2500-SW, AE3200-SW and AE4000-SWA dated 2004-11-12.

Tests carried out

IEC 60947-1, IEC 60947-2. Test sequence I, II and combined.

Environmental tests in accordance with DNV-CG-0339 August 2021.

Marking of product

mitsubishi – Type designation – Electrical data

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the Type approval is complied with and that no alterations are made to the product design or choice of materials.

The main elements of the assessment are:

- Inspection on factory samples, selected at random from the production line (where practicable)
- Results from Routines (RT) checked (if not available tests RT to be carried out)
- Review of type approval documentation
- Review of possible change in design, materials and performance
- Ensuring traceability between manufacturer's product type marking and Type Approval Certificate.

Assessment to be performed at 2 and 3.5 year and at renewal.

END OF CERTIFICATE